PRIMA



PRIMA[™]











SLD 001 (DOOR) TOP ROLLER

SLD 005

FLOOR GUIDE

SLD 002 (TRACK) CENTRE FIXED

SLD 003 (DOOR) BOTTOM ROLLER



SLD 004





DOOR STOPPER





SLD 006

END CAP



SLD 007 I SHAPE CORNER BRACKET





SLA ~ 002 SHOWER DOOR KNOBS



069 🔳

PRIMATM





SLE 001







SLE 003 HANDLE KNOB



SLE 004 FLOOR GUIDE



SLE 005 CORNER LBRACKET SLE 006 BRACKET WT STOPPER SLE 007 L CORNER CONNECTOR







U CHANNEL





ANGLE BRACKET

${\bf SLG}$ frameless folding door system

PRIMA





SLF FRAMELESS FOLDING DOOR SYSTEM



MAXIMUM WEIGHT Per Panel : 90 KGS







SLE-011 Side Hinge Roller

SLE-016



SLF-012 Mid Bottom Guide



SLE-006 Mid Hinge



SLF-017 Side Bottom Guide



SLF-014 Side Bottom Guide



SLE-015 S/S Bottom Track



SLE -001 Aluminium Top Track



SLE-010 Mid Hinge Wt Roller



SLF-013 Mid Hinge Wt Stopper



SLF-018 RH SLE-0181H Side Hinge Bottom Wt Stopper





SLA 002 Sliding Door Handle







SLA 002KD Sliding Door Handle with Key (Glass to Glass)



SLA 002KS Sliding Door Handle with Key (Glass to Wall)












$\mathbf{PRIMA}^{\mathsf{TM}}$





Applications

Suitable for 250kg (max) or 10ft x 9ft x 12mm thk glass panel


Components





075









PRIMA







INSTALLING GLASS



11.5 / 12mm

*The distance for clamp fixing for track.wall fixing: 1.Weight 80kg:max-distance between the clamps= 1/2 the width of the door;

- Weight 80kg-120kg:max-distance between the clamps=1/3 the width of the door;
- Weight 120kg-150kg:max-distance between the clamps=1/4 the width of the door;

Technological data

Daylight opening	Entry width	Door width	Tube length
910-1010mm	800-900mm	880-980mm	2038mm
1010-1110mm	900-1000mm	980-1080mm	2238mm
1110-1210mm	1000-1100mm	1080-1180mm	2438mm
1210-1310mm	1100-1200mm	1180-1280mm	2638mm

W=overpanel width W=sidelight width W=door width

PRIMA

SLC SLIDING DOOR SYSTEM

SLC 1A





Siding Door Roller Max.Glass weight:150kg



Finish









SLC 2





Clamp for pipe connection with wall Material : Stainless Steel 304



SLC 3





Clamp for pipe connection with Top Panel Material : Stainless Steel 304



PRIMA[™]

SLC 4 R/L





















SLC 7





SLC 8







ind Caps for Tube daterial - Stainless Steel 30

Finish : SS

SLC 9





End Caps for tube Material : Stainless Steel 304

Finish : S

SLC 83 T



Installation Tool Material : Stainless Steel 304

inish : SS

SLC 25 TUBES





Tube Size : 3.0 mtr or 6.0 mtr N

Material : Stainless :

Finish : 5

PRIMA

SLC 10





Double Clamp for Pipe Material : Stainless Steel 304 Finit



SLC 11







Double Clamp for Pipe Material : Stainless Steel 304 Finis

SLC12





Clamp for pipe Material : Stainless Steel 304 Finish

SLC 13



025.4

Adjustable Single Clamp Material : Stainless Steel 304







