



# “Dyna-Ken” WT-510 Overhead Stirrer

Shaping the Stirring and homogenizing future....

**Brief Description** The WT510 is a simple, easy to handle and has the ability to achieve quality results quickly. He has the speed and power and suitable for mixture of high viscosity liquid or solid-liquid. Widely used in chemical synthesis, pharmaceutical, physical and chemical analysis, petrochemical, cosmetics, health care, food, biotechnology and other fields..

## Features & Specification

Max. stirring quantity(H <sub>2</sub> O)[L]	20	Operating Environment	0-40°C, 95% rel. humidity
Motor rating input[W]	60	Protection class	IP42
Frequency	110-120V/60Hz , 220-240V / 50-60 Hz	Certified standards	89/336EEC,72/023/EEC, EMC acc. IEC/EN 61000-6-2 / 3, Safety acc. IEC/EN 61010-2-51
Electrical Plug Type	UK Plug,US Plug,European Plug,China CCC Plug	Container Type	50ml tubes,100ml tubes,250ml tubes, small beakers, medium beakers ,large beakers
Speed range (rpm)	0-2200	Warranty	2 years - spare part due to manufacturing defects
Speed control type	Dial knob	Sterilization Method:	All
Speed display	LED	pH Range:	2-13
Dimension LxWxH / ( mm)	83 x 220 x 186	Suitable for solvents & abrasive substances::	YES
Weight (kg)	2.6	Max Viscosity (mPa)	10000
Overload protection	LED lights, motor automatic stops	Motor protect	LED lights, motor automatic stops



## Why purchase our homogenizer ?

### \*Excellent Result For Ultimate Fitness

Max Viscosity : 10,000 mPas



### \*Wide Range of application & Treatable Volume Container

0.2-50 ml as the tissue terror and cell breaker  
 250ml-40,000ml as the high speed mixer  
 10ml – 8,000 ml as the disperser & homogenizer

### \*Competitive advantages in Functional Design

"QUICK CHUCK" Design




to remove or lock the shaft tube in place with an easy quarter-turn. One chuck for all the combination stirrer and agitator.

Highest tip speed 2,200 rpm  
 mean shortest process time to achieve desired result.

### \*Unlimited Customer Support

"Pre-Order Questionnaire" & "Let's trial Run" programme if you suspect the correct equipment to purchase? Let's you help us by fill in the questionnaire or you can ship us the sampls for trial run ! It's totally "FREE"



Dial +1888-312-6992 (tol free for North America,Canada & Putrea Rico) or local line 0173576175 for 7/24 hrs products enquiry online technical support,after sales services and warranty spare parts replacement.

