


GIO★-LITE

GIO-FLEX UR Thermo Transfer Film

GIO-FLEX UR is made with a thin and soft polyurethane film so it is light and stretchable. It perfectly works for the details of artworks and makes the garment unique.

- Recommended Fabric : Cotton, Polyester, Cotton/Polyester Blends, Lycra.



COMPOSITION

PU Resin	34%
Polyurethane Glue	33%
PET Film	33%

APPLICATION INSTRUCTIONS

1. Cut in mirror image through adhesive layer (dull side) to the PET carrier.
2. Weed the unwanted material and lay the cut-design on the fabric.
3. Heat Press at **150°C for 8 seconds** and always **peel cold** (Take off the PET carrier after 15 seconds).



Film



Design & Cut



Weed



Heat Apply

CARE INSTRUCTIONS FOR THE FINISHED PRODUCT



➤ **Washing**

- Washer : Standard Household Washing Machine
Temperature : 60°C
Detergent : Standard Household Detergent
Setting : Colored Clothing without Pre-wash

Maximum washing time on highest temperature not to exceed 12 minutes.
Maximum total washing time not to exceed 50 minutes.
Test fabric for dye migration.

➤ **Bleaching**

Not Recommended

GIO★-LITE

➤ **Drying**

Tumble Dry Low

➤ **Ironing**


Do not use steam, use a cool or warm temperature setting, avoid direct contact of the design, use a press cloth.

COLOR AVAILABILITY

Normal Color



Neon Color



SPECIFICATION

Standard Width	Roll Length	Q'ty / Carton	Weight / Carton	Volume / Carton
510 mm	50 MTS	50 MTS	8.5 KGS	0.013 CBM
510 mm	25 MTS	50 MTS	8.0 KGS	0.020 CBM
1,020 mm	25 MTS	25 MTS	9.0 KGS	0.028 CBM

** Thickness : 70 ~ 80 Micron

STORAGE

- Keep away from the direct sunlight, hot and humid place.
- Use it within 1 year from the date of the lot number (production date).

GIOLITE LUMIAN Co., LTD

RM408, Woolim E Biz Center #1, 170-5,
Guro-Dong, Guro-Gu, Seoul, KOREA
Tel: +82-2-869-1988(Rep.) Fax: +82-2-869-7711
email: giolite@giolite.com
Website: www.giolite.com