



Membrane diffuser tube

Application

- membrane diffuser tube, for industrial and municipal wastewater treatment plant, pressure diffusion with fine bubbles, oxygen input for nitrification in activation basins, permanent and intermittent ventilation
- oxygen input and circulation in xed-bed and bioreactors, thorough mixing of activation basins, sand trap louvre ventilation, renaturation of lakes and rivers, aquacultures, sh farming

Properties

- high energy savings when compared with comparative, market standard EPDM and silicone diffusers due to the much lower pressure loss
- extremely long lifetime and no curing due to the membrane not including a plasticizer
- very wide operating range: normal operation: 3-8, minimum 1, maximum 15 and purging operation 18 Nm³/(h*m_{aer.})
- comparatively high oxygen input and oxygen transfer efficiency even with low density systems

- very fine and uniform bubble formation due to an optimized perforation
- easily and quickly fitted
- extremely tear-resistant and abrasion-resistant (mechanical strength around 2.5-4 times that of most of the EPDM and silicone materials)
- very good resistance to waste water and municipal sewerage in accordance with the latest instructions DWA-M 115
- microbe and hydrolysis resistant
- good resistance to oil, gasoline and chemicals
- conforms to RoHS guideline

Temperature Range

- -40°C to 90°C

Design

- wall: special premium polyurethane (Pre-PUR®)
- wall thickness 0,7 mm approx.

Delivery variants

- further diameters and lengths available on request
- transparent (standard)
- special colours: full coloured

Size	I.D.	Length	Ventilation Length	Weight	Order No.
(mm)	(mm)	(mm)	(mm)	(kg/pcs)	
63	64,5	570	500	0,100	620-0570-2702
63	64,5	820	750	0,150	620-0820-2702
90	91,5	1000	930	0,250	620-1000-2791
90	90,8	1000	910	0,250	620-1000-2794
63	64,5	1070	1000	0,200	620-1070-2702

Accessories



CONNECT 683



CLAMP 682



CONNECT 685



CONNECT 229



CONNECT 684

Overpressure and underpressure are recommended threshold operating values, products can be subjected to higher loads upon request. The bending radius is measured through the inside of the hose arch. The right to make technical modifications is reserved. All values determined at 20°C and are approx.