

Metallographic Sample Grinding Polishing Machine

Model: JG-160



(For reference only)

Features and Application

- Single disc
- Stepless speed changing grinding and polishing with rotating speed from 50 to 1000rpm.
- Used for rough grinding, fine grinding, rough polishing and finishing polishing for specimen preparing.
- Easy to operate, safe and reliable, is an ideal equipment for the labs of plants, research institutes and universities and colleges.



Technical Specifications

Model	JG-160
Diameter of working disc	200mm (203mm is optional)
Working disc rotating speed	50 ~ 1000rpm
Diameter of abrasive paper	200mm
Power supply	220V / 50Hz
Motor power	YSS7124, 550W
Dimension (L x W x H)	730 x 450 x 370mm
Weight	35Kg

Details

