

Metallographic Sample Grinding & Polishing Machine

Model: JG-165



(For reference only)

Features and Application

- Equipped with double motors & double working disks which feature independent controlling. The working disc can be changed and replaced swiftly.
- Two level constant speeds for grinding and polishing, including 300/600rpm.
- With cooling device to cool the sample, thus preventing the damage of the metallographic structure caused by overheat of the sample.
- Applicable to rough grinding, fine grinding, rough polishing and finishing polishing for specimen preparing.

Technical Specifications

Model	JG-165
Diameter of working disc.	203mm (250mm)
Rotating speed of working disc.	300/600rpm
Working voltage	380V/50Hz
Diameter of Abrasive Paper	200mm or 250mm
Motor	Yc712, 120W/250W
Dimension (L x W x H)	700 x 600 x 270mm
Weight	50Kg

