

Metallographic Sample Grinding & Polishing Machine

Model: JG-169



(For reference only)

Features and Application

- Equipped with single disc
- Two rotating speeds, 300rpm and 600rpm
- Equipped with cooling system that can cool down the specimen during pre-grinding so as to prevent overheating and damaging the metallographic structure.
- Applicable to rough grinding, fine grinding, rough polishing and finishing polishing for specimen preparing.
- Ideal option for the lab of factories, science and research institutions and universities.



Technical Specifications

Model	JG-169
Diameter of working disc.	203mm or 250mm
Rotating speed of working disc.	300/600rpm
Working voltage	380V/50Hz
Diameter of Abrasive Paper	200mm (250mm can be customized)
Motor	YSS712, 120W/250W
Dimension (L x W x H)	340 x 650 x 310mm
Weight	30Kg

Details

1. Plate

