

Metallographic Sample Grinding & Polishing Machine

Model: JG-170



(For reference only)

Features and Application

- Equipped with double disc and features two level constant speeds for grinding and polishing, including 300rpm and 600rpm.
- Equipped with cooling system that can cool down the specimen during pre-grinding so as to prevent overheating and damaging the metallographic structure.
- Applicable to rough grinding, fine grinding, rough polishing and finishing polishing for specimen preparing.
- Ideal option for the lab of factories, science and research institutions and universities.

Technical Specifications

Model	JG-170
Diameter of working disc.	200mm
Rotating speed of working disc.	300/600rpm
Working voltage	380V/50Hz
Diameter of Abrasive Paper	200mm
Motor	Yc713, 550W
Dimension (L x W x H)	700 x 600 x 270mm
Weight	45Kg

