

MULTIBASE™ MB50-315

Silicone Masterbatch

DuPont MULTIBASE™ MB50-315 Masterbatch is a pelletized formulation containing 50% of a functionalized ultrahigh molecular weight (UHMW) siloxane polymer dispersed in polycarbonate.

It is designed to be used as an additive in PC compatible systems to impart benefits such as processing improvements and modification of surface characteristics. Liquid siloxane plastic additives have been used for several years to improve the lubricity and flow of thermoplastics. They are effective in this role although some difficulties have been experienced in the incorporation of liquids into thermoplastic melts without the use of specialized equipment. It has also been difficult to produce masterbatches with greater than 20% liquid siloxane because of processing difficulty and bleed problems.

The DuPont MULTIBASE™ MB Series Masterbatches address these problems by supplying a high concentration of an ultra-high molecular weight (UHMW) siloxane as a dispersion in a dry pellet form in a variety of thermoplastics.

Applications

Additive to be used in PC compatible systems

Benefits

When added to PC or similar thermoplastics, at a level of 0.2% to 2%, improved processing and flow of the resin is expected, including better mold filling, less extruder torque, internal lubrication, mold release and faster throughput. At higher addition levels, 2% to 5%, improved surface properties are expected, including lubricity, slip, lower coefficient of friction, and greater mar and abrasion resistance.

The DuPont MULTIBASE™ MB Series Masterbatches are expected to give improved benefits compared to conventional lower molecular weight siloxane additives, e.g., less screw slippage improved release, a lower coefficient of friction, fewer paint and printing problems, and a broader range of performance capabilities.

Product information

Color	White	
Polydimethylsiloxane content	50 %	PhEur 1470
Other properties		
Recommended use level	0.2 - 5 %	
Injection		
Drying Recommended	yes	
Drying Temperature	120 °C	
Drying Time, Dehumidified Dryer	4 h	
Processing Moisture Content	≤0.02 %	

Revised: 2021-02-22 Page: 1 of 2



MULTIBASE™ MB50-315

Silicone Masterbatch

Storage and stability

Shelf life 48 months

Characteristics

Additives Release agent
Compatibility Polycarbonate

Additional information

How to use

DuPont MASTERBATCHES are designed to be processed in the same way as the thermoplastic carrier on which they are based. Masterbatch pellets can be compounded in or added by using a feed hopper during injection molding or extrusion.

Revised: 2021-02-22 Page: 2 of 2

dupont.com

The information set forth herein is furnished free of charge, is based on technical data that DuPont believes to be reliable, and represents typical values that fall within the normal range of properties. This information relates only to the specific material designated and may not be valid for such material used in combination with other materials or in other processes. It is intended for use by persons having technical skill, at their own discretion and risk. This information should not be used to establish specification limits nor used alone as the basis of design. Handling precaution information is given with the understanding that those using it will satisfy themselves that their particular conditions of use present no health or safety hazards and comply with applicable law. Since conditions of product use and disposal are outside our control, we make no warranties, express or implied, and assume no liability in connection with any use of this information. As with any product, evaluation under end-use conditions prior to specification is essential. Nothing herein is to be taken as a license to operate or a recommendation to infringe on patents.

CAUTION: Do not use DuPont materials in medical applications involving implantation in the human body or contact with internal body fluids or tissues unless the material has been provided from DuPont under a written contract or other acknowledgement that is consistent with the DuPont policy regarding medical applications and expressly acknowledges the contemplated use. For further information, please contact your DuPont representative.

DuPont's sole warranty is that our products will meet our standard sales specifications in effect at the time of shipment. Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted. TO THE FULLEST EXTENT PERMITTED BY APPLICABLE LAW, DUPONT SPECIFICALLY DISCLAIMS ANY OTHER EXPRESS OR IMPLIED WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR NON-INFRINGEMENT. DUPONT DISCLAIMS LIABILITY FOR ANY SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

DuPont™, the DuPont Oval Logo, and all trademarks and service marks denoted with ™, SM or ® are owned by affiliates of DuPont de Nemours, Inc. unless otherwise noted. © 2022 DuPont. All rights reserved.