

## TEST SIEVES

Standard: BS 410:1986

### Sampler Grading

Test sieves available in 200 & 300 mm diameter with stainless steel body & either perforated plate or woven wire cloth mesh. A clear rigid design of minimum weight and free from corners where the material could be lodged. An essential feature of our test sieves is flat & uniform mesh with permanent tension round the whole circumference.



Scan To View Full Catalogue



### BRITISH STANDARDS SIEVES

Material: Stainless Steel (BS 410:1986)

Table For Woven Mesh Sieves - Microns (µm)

Nominal Aperture	Model for 200 Diameter	Model for 300 Diameter
20	NL1010 S200W - B001	NL1010 S300W - B001
25	NL1010 S200W - B002	NL1010 S300W - B002
32	NL1010 S200W - B003	NL1010 S300W - B003
36	NL1010 S200W - B004	NL1010 S300W - B004
38	NL1010 S200W - B005	NL1010 S300W - B005
40	NL1010 S200W - B006	NL1010 S300W - B006
45	NL1010 S200W - B007	NL1010 S300W - B007
50	NL1010 S200W - B008	NL1010 S300W - B008
53	NL1010 S200W - B009	NL1010 S300W - B009
56	NL1010 S200W - B010	NL1010 S300W - B010
63	NL1010 S200W - B011	NL1010 S300W - B011
71	NL1010 S200W - B012	NL1010 S300W - B012
75	NL1010 S200W - B013	NL1010 S300W - B013
80	NL1010 S200W - B014	NL1010 S300W - B014
90	NL1010 S200W - B015	NL1010 S300W - B015
100	NL1010 S200W - B016	NL1010 S300W - B016
106	NL1010 S200W - B017	NL1010 S300W - B017
112	NL1010 S200W - B018	NL1010 S300W - B018
125	NL1010 S200W - B019	NL1010 S300W - B019
140	NL1010 S200W - B020	NL1010 S300W - B020
150	NL1010 S200W - B021	NL1010 S300W - B021
160	NL1010 S200W - B022	NL1010 S300W - B022
180	NL1010 S200W - B023	NL1010 S300W - B023
200	NL1010 S200W - B024	NL1010 S300W - B024
212	NL1010 S200W - B025	NL1010 S300W - B025
224	NL1010 S200W - B026	NL1010 S300W - B026
250	NL1010 S200W - B027	NL1010 S300W - B027
280	NL1010 S200W - B028	NL1010 S300W - B028
300	NL1010 S200W - B029	NL1010 S300W - B029
315	NL1010 S200W - B030	NL1010 S300W - B030
355	NL1010 S200W - B031	NL1010 S300W - B031
400	NL1010 S200W - B032	NL1010 S300W - B032
425	NL1010 S200W - B033	NL1010 S300W - B033
450	NL1010 S200W - B034	NL1010 S300W - B034
500	NL1010 S200W - B035	NL1010 S300W - B035
560	NL1010 S200W - B036	NL1010 S300W - B036
600	NL1010 S200W - B037	NL1010 S300W - B037
630	NL1010 S200W - B038	NL1010 S300W - B038
710	NL1010 S200W - B039	NL1010 S300W - B039
800	NL1010 S200W - B040	NL1010 S300W - B040
850	NL1010 S200W - B041	NL1010 S300W - B041
900	NL1010 S200W - B042	NL1010 S300W - B042

Table For Woven Wire Mesh Sieves - Millimeter (mm)

Nominal Aperture	Model for 200 Diameter	Model for 300 Diameter
1.00	NL1010 S200W – B043	NL1010 S300W – B043
1.12	NL1010 S200W – B044	NL1010 S300W – B044
1.18	NL1010 S200W – B045	NL1010 S300W – B045
1.25	NL1010 S200W – B046	NL1010 S300W – B046
1.40	NL1010 S200W – B047	NL1010 S300W – B047
1.60	NL1010 S200W – B048	NL1010 S300W – B048
1.70	NL1010 S200W – B049	NL1010 S300W – B049
1.80	NL1010 S200W – B050	NL1010 S300W – B050
2.00	NL1010 S200W – B051	NL1010 S300W – B051
2.24	NL1010 S200W – B052	NL1010 S300W – B052
2.36	NL1010 S200W – B053	NL1010 S300W – B053
2.50	NL1010 S200W – B054	NL1010 S300W – B054
2.80	NL1010 S200W – B055	NL1010 S300W – B055
3.15	NL1010 S200W – B056	NL1010 S300W – B056
3.35	NL1010 S200W – B057	NL1010 S300W – B057
3.55	NL1010 S200W – B058	NL1010 S300W – B058

Table For Lid & Pan Sieves

Model for 200 Diameter	Model for 300 Diameter
NL1010 S200P – B001	NL1010 S300P – B001

### Stainless Steel Wash Sieve

200 mm Diameter x 200 mm High

Model No	Aperture
NL 1037 S200 – WS1	2 mm
NL 1037 S200 – WS2	75 µm
NL 1037 S200 – WS3	63 µm


### Optional Accessories :

Model No	Accessories Description
NL 7041 X / 004	Sieve Brush – Double End Brass / Nylon
NL 7041 X / 005	Sieve Brush – Double End Soft / Hard Nylon
NL 7041 X / 008	Sieve Brush – Double End Round Soft / Hard Nylon
NL 1010 X / SR1	Test Sieve Shelves


Table For Perforated Plate (Square Holes) - Millimeter (mm)

Nominal Aperture	Model for 200 Diameter	Model for 300 Diameter
4.00	NL1010 S200Q – B002	NL1010 S300Q – B002
4.50	NL1010 S200Q – B003	NL1010 S300Q – B003
4.75	NL1010 S200Q – B004	NL1010 S300Q – B004
5.00	NL1010 S200Q – B005	NL1010 S300Q – B005
5.60	NL1010 S200Q – B006	NL1010 S300Q – B006
6.30	NL1010 S200Q – B007	NL1010 S300Q – B007
6.70	NL1010 S200Q – B008	NL1010 S300Q – B008
7.10	NL1010 S200Q – B009	NL1010 S300Q – B009
8.00	NL1010 S200Q – B010	NL1010 S300Q – B010
9.00	NL1010 S200Q – B011	NL1010 S300Q – B011
9.50	NL1010 S200Q – B012	NL1010 S300Q – B012
10.00	NL1010 S200Q – B013	NL1010 S300Q – B013
11.20	NL1010 S200Q – B014	NL1010 S300Q – B014
12.50	NL1010 S200Q – B015	NL1010 S300Q – B015
13.20	NL1010 S200Q – B016	NL1010 S300Q – B016
14.00	NL1010 S200Q – B017	NL1010 S300Q – B017
16.00	NL1010 S200Q – B018	NL1010 S300Q – B018
18.00	NL1010 S200Q – B019	NL1010 S300Q – B019
19.00	NL1010 S200Q – B020	NL1010 S300Q – B020
20.00	NL1010 S200Q – B021	NL1010 S300Q – B021
22.40	NL1010 S200Q – B022	NL1010 S300Q – B022
25.00	NL1010 S200Q – B023	NL1010 S300Q – B023
26.50	NL1010 S200Q – B024	NL1010 S300Q – B024
28.00	NL1010 S200Q – B025	NL1010 S300Q – B025
31.50	NL1010 S200Q – B026	NL1010 S300Q – B026
35.50	NL1010 S200Q – B027	NL1010 S300Q – B027
37.50	NL1010 S200Q – B028	NL1010 S300Q – B028
40.00	NL1010 S200Q – B029	NL1010 S300Q – B029
45.00	NL1010 S200Q – B030	NL1010 S300Q – B030
50.00	NL1010 S200Q – B031	NL1010 S300Q – B031
53.00	NL1010 S200Q – B032	NL1010 S300Q – B032
56.00	NL1010 S200Q – B033	NL1010 S300Q – B033
63.00	NL1010 S200Q – B034	NL1010 S300Q – B034
71.00	NL1010 S200Q – B035	NL1010 S300Q – B035
75.00	NL1010 S200Q – B036	NL1010 S300Q – B036
80.00	NL1010 S200Q – B037	NL1010 S300Q – B037
90.00	NL1010 S200Q – B038	NL1010 S300Q – B038
100.00	NL1010 S200Q – B039	NL1010 S300Q – B039
106.00	NL1010 S200Q – B040	NL1010 S300Q – B040
112.00	NL1010 S200Q – B041	NL1010 S300Q – B041
125.00	NL1010 S200Q – B042	NL1010 S300Q – B042

### Test Sieves Rack



Multi Size Sieves



Mount To Wall



Stacking Shelves